



Magnetic (Gen 4) 8m/26ft-30

TAPE MEASURE MAGNETIC (GEN IV)

- Standout: Measure distances in the air of up to 4.5 m.
- Straighter stiffer blade for more precise measurement of long distances in the air.
- Blade width of 30 mm ensures blade stability and stiffness.
- Smoothest blade retraction with more speed and less blade rollover.
- Finger-Stop feature for quick, controlled retraction of the blade.
- Highest blade durability with Double-Sided Anti-Tear coating for the first 15 cm of the blade.
- Impact resistant body for the toughest conditions on the job site.
- Double-Sided printing with vertical and horizontal scale for versatile measurements.
- Architectural scale to measure scaled drawings, such as blueprints.
- Strong magnetic hook for maximum holding power.
- Available lengths: 5m, 5m/16ft, 8m, 8m/26ft.



Article Number	4932498771
Blade width (mm)	30
Length [m]	8 / 26ft
Magnetic	Yes
Pack quantity	1