

BJ ROUND BRAID WITH CRIMPED LUGS



CERTIFICATIONS



FEATURES

- Ready to use out of the box, saving installation time and labor
- Allows for bending very close to the contact area
- RoHS compliant

SPECIFICATIONS


- Material:** Copper
- Finish:** Tinned
- Working Temperature:** 221 °F Max

| Table 1/2 | | | | | | |
|----------------|----------------|----------|---------------|------------|---------------|----------------|
| Catalog Number | Article Number | Ampacity | Cross Section | Length (L) | Wire Diameter | Hole Size (HS) |
| BJ10-300S | 556920 | 75A | 19.74 | 11.81" | 0.01" | 0.26" |
| BJ6-150S | 556900 | 45A | 11.84 | 5.91" | 0.01" | 0.26" |
| BJ6-200S | 556910 | 45A | 11.84 | 7.87" | 0.01" | 0.26" |

| Table 2/2 | | |
|----------------|----------------|-------------|
| Catalog Number | Article Number | Unit Weight |

| | | |
|-----------|--------|---------|
| BJ10-300S | 556920 | 0.07 lb |
| BJ6-150S | 556900 | 0.02 lb |
| BJ6-200S | 556910 | 0.03 lb |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500