

NEW

skater

PRODUCT CHARACTERISTICS



High resistance to heat and tearing



Non-magnetic



EVA sole for maximum comfort

S3 EN ISO 20345: 2011 SRC
HRO








HEEL REINFORCEMENT FOR MORE SUPPORT

■ 8824 BLACK | SIZE: 39 TO 48

COMPOSITION

| | |
|-----------------------|----------------------------------------------------|
| Upper | Microfibre + Split leather |
| Lining | Fabric |
| Toe Cap | Composite |
| Stay clean insole | Mesh over PU foam. Removable. Anatomically shaped. |
| Puncture proof insert | Non-metallic |
| Sole | Rubber / EVA |
| Weight for size 42* | 588g * Weight per shoe |

SAFETY TABLE

| | |
|-------------------------------------------------------------------------------------|-----------------------------|
|  | Toe cap (200J) |
|  | Antipuncture sole |
|  | Antislip sole ** |
|  | Shock-absorption |
|  | Antistatic |
|  | Oil and fuel resistant shoe |
|  | Water-repellent upper |

**

| Size coefficient 42 | Flat | | Heel | |
|------------------------------------------|----------|--------|----------|--------|
| | Standard | Parade | Standard | Parade |
| SRA ceramic floor / Nals (soap solution) | 0,32 | 0,44 | 0,28 | 0,40 |
| SRB Steel / Glycerine (oil) | 0,18 | 0,18 | 0,13 | 0,16 |