

Eaton 16NHG000B-690

Catalog Number: 16NHG000B-690

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 690V, 16A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	16NHG000B-690
	EAN
	5027590437714
UPC	Product Length/Depth
051712188395	79 mm
Product Height	Product Width
51 mm	21 mm
Product Weight	Compliances
151.3333333 g	RoHS Compliant
	CE Marked
Certifications	
IEC 60269-1	
IEC 60269-2	
DIN 43620	



Product specifications

Type

Fuse

Special features

Live gripping lug

Application

industrial

Utilities, Solar, Wind

Amperage Rating

16 A

Fitted with:

Metal gripping lugs

Fuse size

NH000

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

690 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Resources

Catalogs

CA134002EN

NH Fuse links, bases and gear

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Declarations of conformity

UKCA NH Size 000, 690V fuse-links

[DA-DC-00005065.pdf](#)

[DA-DC-00005063.pdf](#)

eCAD model

[eaton-low-voltage-nh-fuse-eplan-16nhg000b-690.edz](#)

Multimedia

Eaton Bussmann – NH fuse link portfolio

Presentations

NH Overview Video

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Watt losses

2.5 W

Connection

Blade end

Construction

NH000

Construction size

NH000

Fuse shape

Square body

Knife blade contacts

Voltage type

AC

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Material

Ceramic body

Packaging type

Standard

Quantity

3

Voltage rating

690 V

Rated switching capacity AC

120 kA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia