

## Specifications for BMP51/53 Labelmaker Tape

<b>Adhesive</b>	Permanent Acrylic
<b>Application</b>	Control Panel & Electrical Panel Labels; Bin & Storage Identification; General & Industrial Identification; Indoor & Outdoor Grade Facility & Safety Identification
<b>Article No.</b>	143402
<b>Brady Material No.</b>	<a href="#">B-595</a>
<b>Material Type</b>	Vinyl
<b>Colour</b>	White on Red
<b>Finish</b>	Gloss
<b>Description</b>	Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper jacketed pipes, powder coated surfaces). Also adheres to difficult low energy surface items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics)
<b>Max. Service Temp. °C</b>	82
<b>Order Reference</b>	MC-1500-595-RD-WT
<b>Printer Compatibility</b>	BMP51; BMP53
<b>Shape</b>	Continuous
<b>Size - Length (m)</b>	7.62
<b>Size - Width (mm)</b>	38.10
<b>Total Qty per Pack</b>	1 Label(s) / Box
<b>Voice/Data Application</b>	Backbone Labeling
<b>Industry</b>	Electrical; Facility & Safety Identification; Process
<b>Layout</b>	Continuous Roll
<b>Min. Application Temp. °C</b>	-18
<b>Min. Service Temp. °C</b>	-40
<b>Thickness (mm)</b>	0.1