

Features

- Strong and durable diecast zinc construction
- 90-degree quarter-turn rotation
- 6mm square lock type and key included
- Simple and secure installation
- IP54 rated

RS PRO Quarter-Turn Camlock, Diecast Zinc Body, Zinc Plated Steel Cam, 6mm Square, IP54 Rated

RS Stock No.: 0517862



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

A strong and durable cabinet lock which is ideal for enclosures, electrical cabinets and furniture. This camlock features a 6mm square lock and corresponding key which ensures security and easy opening and closing. The main housing is diecast from zinc and the steel cam is zinc plated. The camlock opens and locks with a quarter-turn.

General Specifications

Cam length	24
Panel to tongue depth	12.5
Material	Diecast zinc and zinc plated steel
Opening angle	90 degrees
Colour	Silver
Application	Enclosures, HVAC, machinery, equipment, construction industry

Mechanical Specifications

A	20
B	4
C	2
D	12
E	6
F	24
G	12.5

