



Notes: (Unless Otherwise Specified)

1. Waterproof Rate: IP67.
2. Recommend Panel Thickness: 0.8 to 6.0 mm.
3. Recommend Torque: 19-20 Kgf-cm.
4. Mating Cap P/N: 125-7924
5. RoHS Compliant.

REV	ECN#	DESCRIPTION OF REVISION	DRAW BY DATE	CHECK BY DATE	APPROVE BY DATE
A0	ECN-130403	Mass Production	Joyce 04/02/13	Lucas 04/02/13	Roy 04/02/13
A1	ECN-140805	Modify Item 9, Shrink Tube L=10mm to 20mm	Joyce 08/07/14	Lucas 08/07/14	Roy 09/07/14



10	Cable	UL2725 IP*28AWG+2C*24AWG+H/My+D+B Color: Black, OD=5.0mm	1
9	Shrink Tube	L=20mm Color: Black	1
8	Over Mold	PVC Color: Black	1
7	USB-A Plug	Housing: Thermoplastic, Color: Black Contacts: Copper Alloy, Finish: Au Plated Shell: Cold Roll Steel, Finish: Ni Plated	1
6	Glue	Epoxy Color: Black	1
5	PCB	FR-4 Color: —	1
4	USB-A Receptacle	Housing: Thermoplastic, Color: Black Contacts: Copper Alloy, Finish: Au Plated Shell: Copper Alloy, Finish: Ni Plated	1
3	Gasket	Silicone Color: Black	1
2	Hex Nut	Thermoplastic Color: Black	1
1	Housing	Thermoplastic Color: Black	1
Item	Part Name	Material / Finish	QTY



Recommend
Panel Cut-Out



Wiring Diagram

Mating Part:
111-6752

TITLE									
USB-A Plastic C4 Panel Jack Lock With Cable + USB-A Plug									
	B	1:1	David 06/21/10	Roy 06/21/10	Roy 06/21/10	X.X ± 0.5	X.XXX ± 0.05	mm	1/1
THIRD ANGLE PROJECTION	SIZE	SCALE	DRAW / DATE	CHECK / DATE	APPROVE / DATE	TOLERANCES		UNIT	SHEET

RS Stock No
111-6748