

# R 15-STI-C-0,5 QMM-AWG 20



Part number 09 15 000 6103

Specification R 15-STI-C-0,5 QMM-AWG 20

HARTING eCatalogue https://b2b.harting.com/09150006103

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

#### Version

Manufacturing process Turned contacts	Gender	Male
	Manufacturing process	Turned contacts

#### Technical characteristics

Conductor cross-section	0.5 mm²
Conductor cross-section	AWG 20
Operating current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



# Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1
Specifications	IEC 61984

#### Commercial data

Packaging size	100
Net weight	0.698 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors