

## Features

- Anti-drill centre for added protection
- Highly durable brass construction with chrome plating
- Medium physical and manipulation resistance
- Optional key registration for optimal control
- Suitable for both indoor or outdoor use
- 500,000 key differs
- Choice of four body lengths

## RS PRO Camlocks

RS Stock No.: 0630959



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

*This lock offers a combination of good security, excellent key control and a very high build quality. It offers over 500,000 different key combinations, an all-brass construction, high durability from its chrome plated outer body and an anti-drill centre to provide added security*

- *Supplied with 2 keys per lock*
- *Anti-drill centre for added protection*
- *Medium physical and manipulation resistance*
- *Suitable for both indoor and outdoor use*

## General Specifications

Features	Durable brass cam lock
Key Differ	500,000
Mechanism	Seven Pin Unique Radial Pin Tumbler
Body Material	Brass
Finish	Polished Chrome
Key Suite Options	Keyed alike and keyed to differ
Body Length	13mm, 18mm, 25mm and 30mm
Fixing Hole Dimensions	Standard 19.1mm x 15mm double D punch
Lock Fixing	2BN brass body nut (supplied except 13mm) and a nyloc tail nut
Key Operations	3, 6 and 9 12 o'clock trapped and free key

## Mechanical Specifications

Unlock Method	90 degrees clockwise turn, key trapped
Lock Type	Cam lock