




# WATER PUMP / UNIVERSAL PLIERS



# 142 Universal pliers






### 142

#### **UNIVERSAL PLIERS**

- Acc. to DIN ISO 8976 Form C
- ▼ With safety box joint and protection against blocking
- ▼ Fine adjustment
- ► 1427 = 17 settings
- ▼ 142 10 = 15 settings
- ▼ 142 12 = 17 settings
- ▼ Single-hand push-button adjustment
- ▶ Long slim jaws
- ▼ Offset gripping faces for self-gripping of nuts and pipes
- **▼** GEDORE special chrome-vanadium steel
- ▼ Induction-rehardened serrated faces
- ▼ Model C = slim handles with forged serrations
- ▼ Model TL = agate-grey, with blue dipped handle protectors
- ▼ Model JC = chrome-plated, 2-component handles








	В.	30	-				-	
L <sub>1</sub>	L <sub>2</sub>	b	h	mm [j]	<b>∆</b> 200 €	Code	No.	
180	32	6.5	40	37	0.183	2668211	142 7 TL	
180	32	6.5	40	37	0.173	2668238	1427C	
255	39	7.5	48	38	0.371	6416180	142 10 TL	
250	39	7.5	48	38	0.380	6416260	142 10 C	
260	39	7.5	48	38	0.417	6416340	142 10 JC	
300	43	8.5	55	44	0.550	1005413	142 12 TI	

# **UNIVERSAL PLIERS 6 settings**

- Acc. to DIN ISO 8976 Form B
- ▼ Slim head
- ▼ Forged twin-groove lay-on slip joint and toothed recess
- Offset gripping faces for self-gripping of nuts and pipes
- ▼ With finger protection
- For pipes up to 1.1/2" and nuts up to 38 mm
- ▼ GEDORE special chrome-vanadium steel, chrome-plated
- ▼ Induction-rehardened serrated faces
- ▼ Model C = slim handles with forged serrations
- ▼ Model JC = chrome-plated, 2-component handles





L <sub>1</sub>	L,	ь	h	mm [i]	∆. d	Code	No.
256	40	10.6	56	38	0.340	6410650	143 10 C
262	40	10.6	56	38	0.390	6415880	143 10 JC





