




0402 - BALL VALVE DOUBLE FEMALE



| | |
|---------------------------------|---|
| maximum working pressure | 40 bar 4 MPa 580 psi |
| working temperature | -20 to 80 °C -4 to 176 °F 253 to 353 °K |
| body | NICKEL PLATED BRASS |
| retaining nut | NICKEL PLATED BRASS |
| stem | BRASS |
| stem seal | NBR |
| 'O'-rings | NBR |
| ball seal | NBR |
| handle | ZAMAK |

| Part Nb | C | E (mm) F (mm) F1 (mm) H (mm) H1 (mm) L (mm) L1 (mm) M (mm)  (kg) | | | | | | | | |
|------------|--------|---|-----|-----|-----|-----|-----|-----|-----|-------|
| | | All | All | All | All | All | All | All | All | All |
| 0402 04 10 | G1/8 | 8 | X | 14 | 35 | 29 | 44 | 25 | 48 | .094 |
| 0402 07 10 | G1/8 | 8 | 19 | 19 | 38 | 31 | 51 | 27 | 48 | .165 |
| 0402 07 13 | G1/4 | 12 | 19 | 19 | 38 | 31 | 53 | 28 | 48 | .156 |
| 0402 10 17 | G3/8 | 12 | 24 | 24 | 45 | 43 | 59 | 31 | 69 | .244 |
| 0402 13 21 | G1/2 | 15 | 27 | 27 | 47 | 44 | 67 | 34 | 69 | .292 |
| 0402 20 27 | G3/4 | 16.5 | 32 | 38 | 63 | 54 | 80 | 39 | 108 | .655 |
| 0402 23 34 | G1 | 19 | 41 | 46 | 67 | 57 | 94 | 47 | 108 | 1.036 |
| 0402 32 42 | G1 1/4 | 21.5 | 55 | 60 | 97 | 115 | 112 | 59 | 180 | 2.467 |
| 0402 32 49 | G1 1/2 | 22 | 55 | 60 | 97 | 115 | 120 | 62 | 180 | 2.34 |
| 0402 40 48 | G2 | 26 | 70 | 70 | 104 | X | 122 | 61 | 190 | 2.614 |
| 0402 40 49 | G1 1/2 | 22 | 55 | 55 | 104 | X | 111 | 55 | 190 | 2.445 |