



Part Number : [2074590003](#)
Product Description : KK Plus 396 Terminal Position Assurance (TPA) Retainer, 3 Circuits, Natural
Series Number : 207459
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[2074590003_sd.pdf](#)
[2074590000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2074580000-AS-000.pdf](#)
[2074580000-PS-000.pdf](#)
[2074580000-PS-CH-000.pdf](#)
[2074580000-PS-ES-000.pdf](#)
[2074580000-PS-JP-000.pdf](#)
[2074580000-PS-SK-000.pdf](#)
[2074580000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	207459
Description	KK Plus 396 Terminal Position Assurance (TPA) Retainer, 3 Circuits, Natural
Component Type	Terminal Position Assurance
Product Name	KK Plus
UPC	191130115822

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon

Net Weight	0.108/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
KK Plus 396 Single Row Receptacle Housings	<u>207458</u>