

18VX2 LAWNMOWER 43CM LXT DLM432Z

DM432 is a 430mm (17") push type cordless lawn mowers with plastic deck, and powered by two 18V LXT Li-Ion batteries in series.

Recommended for lawns up to 575m²



TECHNICAL SPECIFICATIONS

Battery Type	Li-ion
Body only machine	✓
Voltage	36 (18v x2) v
Noise sound pressure	81 dB(A)
Noise sound power	92 dB(A)
Noise K factor	3 dB(A)
Blade type	Rotary type 2 tooth
Cutting diameter	430 mm
Cutting heights	13 / 20-75 Levels/ mm
Collection box	50 litres
No Load Speed	3600 rpm
Vibration K factor	1.5 m/sec ²
Vibration	2.5 m/sec ²
Net weight	16.8 – 17.5 kg

USER BENEFITS

- Electric brake
- Soft start
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Single lever cutting height adjustment
- Grass box with grass level indicator
- Rubberised handle bar
- Low noise and vibration

[Link to product - makitauk.com](https://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER