

STREAM DESKTOP COMFORT

The wireless desktop set – Ergonomic and quiet working at its best



Models may vary from the image shown

Discover the CHERRY STREAM DESKTOP COMFORT – your ergonomic and reliable desktop set for an optimal working environment!

Mouse & keyboard: Bundled ergonomics for a comfortable working environment

The STREAM DESKTOP combines two top performers. The wireless keyboard is based in its design on the STREAM KEYBOARD, one of the world's best-selling keyboards. In the STREAM DESKTOP COMFORT bundle, it has the perfect partner with the new ergonomic wireless mouse. The mouse is especially suitable for medium to large hands and offers a variety of benefits for the health and well-being of the user. The ergonomic design of the optical right-hand mouse promotes a natural hand position, which can help to minimize the risk of wrist pain or carpal tunnel syndrome. The keyboard meets all pertaining ergonomic requirements. In addition, the integrated and rubberized feet of the keyboard support the overall ergonomics.

SX scissor technology and whisper-quiet mouse buttons: The ideal symbiosis

The flat wireless keyboard of the desktop set features our innovative CHERRY SX scissor technology, which ensures a precise and whisper-

quiet keystroke. The mouse buttons, which are also very quiet, complement this working environment by enabling virtually silent operation. Together, the keyboard and mouse offer a solution for a quiet workplace.

Wireless & versatile: Maximum range and versatility with CHERRY KEYS

The 2.4 GHz wireless technology of the mouse and keyboard offers an impressive range of up to 10 meters, allowing you to work freely. With the ergonomic, 6-button computer mouse at your side, you can navigate effortlessly through your everyday work. The PC mouse's front and back buttons located at the side are especially helpful and increase your productivity.

For even more versatility, use the free CHERRY KEYS software. This is available for download at www.cherry.de. CHERRY KEYS allows you to customize your keyboard or mouse with just a few clicks.

Reliability and function combined: CHERRY quality right on your desk

CHERRY has always placed special emphasis on reliability and functionality. The keyboard stands stable like a rock on the desk thanks to the integrated metal plate and does not slip during typing. The mouse, on the other hand, moves effortlessly over the desk. With a high-quality mouse wheel made of metal, it not only offers an attractive feel, but also durable quality. The large sliding pads on the underside provide optimal gliding, guaranteeing precise movements and comfortable use.

In terms of battery life, the STREAM DESKTOP COMFORT once again scores points. With an impressive battery life of up to 36 months, it is the perfect choice for frequent users. The integrated status LEDs for Caps Lock, Num Lock and Scroll Lock give clear signals when a battery change is required.

Safety & sustainability: Desktop set with GS seal and "Blue Angel" label

Our desktop set not only meets the highest demands for performance, but also for safety and environmental responsibility. The "Tested for Safety"

GS seal takes into account all relevant European directives and regulations designed to protect your health. It also proudly bears the “Blue Angel”, a German award for particularly sustainable products.

Choose STREAM DESKTOP COMFORT - a wireless set that not only meets your expectations, but exceeds them. Eliminate cable clutter with innovative technology, ergonomics, and environmental awareness for a productive, quiet, and sustainable workplace.

FUNCTION AND PERFORMANCE

- Flat keyboard with CHERRY SX scissor mechanism
- Whisper quiet: Keystroke and mouse buttons
- Ergonomic right-hand mouse with 6 buttons and scroll wheel
- Mouse with rubberized thumb rest in trendy Varanoi look
- 4-level adjustable mouse sensor with up to 4000 dpi
- High-quality metal mouse wheel ensures a pleasant feel and precise scrolling
- Keyboard with rubberized feet for perfect slip resistance
- Keyboard and mouse with AES-128 encryption
- Battery life up to 36 months (keyboard: 36 months, mouse: 16 months)
- Status LEDs show low battery charge and mouse resolution
- Keyboard with integrated status LEDs for the CAPS LOCK, NUM and SCROLL keys
- Keyboard with 10 office & multimedia keys
- “Blue Angel” environmental label & GS approval (full-size layout)

TECHNICAL DATA

Colour:	black
Weight main product:	925 g

Weight of product without packaging:	1,020 g
Weight of product incl. packaging:	1,470 g
Weight of master carton incl. content:	8,390 g
Content of master carton (pieces):	5
Dimensions product without packaging:	462,2 mm x 162,2 mm x 23,1 mm
Dimensions product incl. packaging:	573 mm x 190 mm x 60 mm
Dimensions master carton:	600 mm x 305 mm x 215 mm
Storage temperature:	-20 °C - 65 °C
Working temperature:	0 °C - 50 °C
Product approvals:	• Blauer Engel • CE • China RoHS • FCC • GS • Windows Hardware Compatibility • EU RoHS • UKCA • REACH • VDE
Awards & Certificates:	• Blauer Engel • VDE-GS
System Requirements-Hardware:	USB-A
Operating system:	• Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	• Manual • Mouse • Keyboard • Nano-USB-Receiver • 3 x AA battery
Reliability:	MTBF > 10 Mio. h calculated to SN 29500 (electronic module only)
Software support:	CHERRY KEYS
USB dongle:	yes

2.4 Ghz wireless connection:	yes
Encryption in wireless mode:	yes
Wireless range:	10 m
Connection via Bluetooth:	no
Number of batteries:	2
Battery type:	Alkaline
Battery design:	AA
Battery rechargeable:	no
Battery replaceable:	yes
Service life per key (in million strokes):	20 mio. actuations
Max. current consumption (mA) of keyboard:	16 mA
Keyboard format:	Full-size (100%)
Integrated metal plate:	yes
Volume (dB) of keyboard:	49 db
N-Key Rollover:	no
Anti-ghosting:	no
Key encryption:	AES-128
Internal memory:	no
Actuating force (cN):	65 cN
Actuating force tol.:	10 cN
Total Key Travel:	2,8 mm
Key labeling:	Pad Printing + UV coating
Palm rest:	Palm rest available as accessory
USB-Hub:	no
Number of keys:	105 + 10
Special key functions:	• PC lock • Browser • e-mail program • Calculator • Volume down • Volume up • Play/Pause • Next track • Last track
Illumination:	no
Adjustable feet:	integrated
Status LEDs:	in keys

Key technology:	Scissor
Keycap material:	ABS
EAN:	4025112103636
Model number:	JD-85K
Protection class:	Standard
Warranty:	1 additional year voluntary limited manufacturers warranty
Layout:	GB (United Kingdom)

TECHNICAL DATA (MOUSE)

Colour (Mouse):	black
Dimensions mouse without packaging:	126,7 mm x 85,2 mm x 49,7 mm
Number of keys:	6
Thumb buttons:	yes
Sensor:	PAW3222LU-TJDU SENSOR SMD 8PIN
Max. resolution (dpi):	4.000 dpi
dpi switch:	yes
dpi levels:	4
Housing material:	ABS
Max. Current consumption (mA) Mouse:	16 mA
Switch type:	silent
2.4 Ghz wireless connection:	yes
Wireless range:	10 m
Encryption in wireless mode:	AES-128
Connection via Bluetooth:	no
Number of batteries in mouse:	1
Battery type:	Alkaline
Battery design:	AA
Battery rechargeable:	no
Battery replaceable:	yes

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.