



Product data sheet

Power tools for trade & industry

Cordless Rivet Gun

PRO GRG 18V-16 C



Versatile: one rivet gun for a wide range of rivets and with two riveting modes

The most important data

Voltage	18 V
Rivet diameter	3 - 6.4 mm
Pull force, max.	16,000 N

Part Number 0 601 9K5 000

Technical data

Technical data

Weight excl. battery	1.6 kg
Pull force, max.	16,000 N
Stroke length	0 - 25 mm
Rivet diameter	3 - 6.4 mm
Tool dimensions	290 x 243 x 67 mm
Voltage	18 V

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cordless convenience ensures greater on-site mobility and lower set-up cost
- As powerful and versatile as a pneumatic tool for 3 to 6.4 mm diameter rivets
- Long battery runtime for pulling 1,000 rivets on a single charge
- AUTO and MANUAL rivet function for personal preference during application



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

