

# LED LENSER® X14

This stylish larger-bodied power torch for professional users embraces the best of modern light technology and delivers mighty bright performance from two synchronised front lights, developed using X-Lens Technology. Together they produce an intense single circular white beam generating an astounding 450 lumens of light and capable of penetration to 350 metres. It is the kind of light that might be needed to illuminate underground rail lines, dark country lanes or multi-storey lift shafts. A Speed Focus switch on the metal barrel makes it quick and easy to glide from flood to spot beam for wide-view or pinpoint illumination. At all times the light remains glare-free, flawless and consistent thanks to the patented Advanced Focus System, which controls and directs the light in to spot or flood beam without any distracting concentric circles or black holes. Through Smart Light Technology there is a choice of energy modes, light programmes and functions to help preserve or tailor light to any given situation. These functions are controllable from a single Dynamic Switch at the end of the barrel and include Dim, SOS, Low Power and Defence Strobe. The torch uses 4 x AA batteries (included), which have their own gold-plated contacts to maximise efficient energy transmission. Also supplied is a wrist strap and 360-degree hands-free belt clip.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Medium sized, dual lens LED hand-held torch with advanced optics.
- Energy efficient CREE® Power+ LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology™. Micro-chip controlled multi-option technology. Two energy usage modes, three pre-set light programs and eight light options (Morse, Dim, Boost, Power, Low Power, Blink, SOS, Defence Strobe)
- X-Lens Technology™. Multiple lenses perfectly calibrated to produce an awesome single beam
- Speed Focus™ with Fast Lock™. Instant, smooth, stage-less, single-handed beam selection. Position lock to prevent beam accidentally refocusing
- Dynamic Switch™ - Reactive, single switch control
- Large beam width due to larger head size
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant. IPX54

## Technical Information

Size: 181 x 83mm Ø

Power: 450 lumens max

Run Time: up to 10 hours

Beam Distance: up to 350m

Weight: 420grams

Supplied with : Wrist-strap, 360° Belt-clip and Duracell® batteries (4xAA)

Code	Colour	Packaging	Barcode
8415X	Black	Gift Box	4029113841504