

EKJ 80-G-2FSH



Sample image

Order symbol : EKJ 80-G-2FSH

Product nr : 3530556

Description : Hinged cover, PC

Remarks : Grey

EAN : 6418074010407

El. number :

- Finland : 3422756
- Denmark : 8212012778
- Sweden : 2538227

Dimensions :	Height	Width	Depth
mm :	280	190	80
inch :	11.02	7.48	3.15

Materials :

Material :	Polycarbonate
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175