

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, with bore hole, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 6, text field height: 15 mm, text field width: 30 mm

Commercial data

Item number	0803874
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2419
Product key	BG2419
Catalog page	Page 316 (C-3-2019)
GTIN	4055626173337
Weight per piece (including packing)	17 g
Weight per piece (excluding packing)	17 g
Customs tariff number	39199080
Country of origin	DE

US-EMLP-HA 24 (30X15/12,5) - Plastic label



0803874

<https://www.phoenixcontact.com/gb/products/0803874>

Technical data

Product properties

Product type	Device marking
Product property	highly adhesive

Marking

Number of individual labels	6
Number of individual labels per row	3
Identification technology	Thermal transfer for sheets and cards, UV LED technology

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
---------------	--

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	30 mm
Length	66 mm
Material strength	0.63 mm

Text field

Text field width	30 mm
Text field height	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMLP-HA 24 (30X15/12,5) - Plastic label



0803874

<https://www.phoenixcontact.com/gb/products/0803874>

Classifications

ECLASS

ECLASS-13.0	27281103
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-EMLP-HA 24 (30X15/12,5) - Plastic label



0803874
<https://www.phoenixcontact.com/gb/products/0803874>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk