

## FEATURES

- **Heat Stabilised Material:**  
Ensures durability and performance in high-temperature environments up to 105°C
- **UL 94 V-2 Fire Behaviour:**  
Provides a level of flame retardancy for added safety
- **Tensile Strength of 22 kg:**  
Offers robust holding capability for secure bundling
- **Maximum Bundle Diameter of 52 mm:**  
Accommodates a wide range of cable sizes
- **Nylon Construction:**  
Provides strength and flexibility for various applications

## RS PRO 203mm Nylon Cable Tie, Heat Stabilised

RS Stock No: 656-019



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 203mm Nylon Cable Tie is designed for secure and efficient cable management. Ideal for bundling cables and wires, this heat-stabilised cable tie offers reliable performance in various environments, ensuring organised and safe installations.

### General Specifications

Colour	Light Green
Product Type	Cable Tie
Sub Type	Heat Stabilised
Tensile Strength	22 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

### Mechanical Specifications

Length	203 mm
Material	Nylon
Maximum Bundle Diameter	52 mm
Width	4.6 mm

### Operation Environment Specifications

Maximum Operating Temperature	105 °C
-------------------------------	--------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---