

scratch brush curved HBG 1 row stainless steel wire dia. 0.30 (10)



scratch brush curved HBG 1 row stainless steel wire dia.
0.30 (10)

Item number: 43662003

EAN: 4007220153734

PFERD TOOLS offers an extensive range of scratch brushes with various shapes and filament materials.

Excellent for cleaning work in hard-to-reach areas, e.g. angles, corners and pipes.

In order to fulfil the particular requirements for working with stainless steel (INOX), PFERD TOOLS uses wire quality 1.4310/1.4301 (V2A) for all INOX brushes. Practical experience from industry has shown that this offers very good corrosion resistance with an optimum tool life. All PFERD TOOLS brushes with INOX filaments are colour-coded in blue and are suitable for use on all stainless steels (INOX), such as V4A. The wire quality 1.4310/1.4301 tends to become ferromagnetic in the case of cold working; i.e. it can be attracted using magnets. The reason for this is a change in the microstructure caused by deformation (e.g. during the wire drawing process). This does not have any impact on the quality and corrosion resistance of the INOX filament. The filament is still resistant to corrosion.

Stainless steel wire (INOX) withstands temperatures up to 450 °C.

Technical information

Dia. filament material	0.3 mm
Filament material	Stainless steel wire (INOX)
Length, filament	25 mm
Length, total	265 mm
Mounting system	Manual use
Number, rows	1

Advantages

- ✓ Very good corrosion resistance.

Materials that can be worked

- ✓ Aluminium
- ✓ Bronze
- ✓ Cobalt-based alloys
- ✓ Hard non-ferrous metal
- ✓ Other non-ferrous metals
- ✓ Stainless steel (INOX)
- ✓ Wood

Applications

- ✓ Cleaning
- ✓ Derusting
- ✓ Paint stripping
- ✓ Removing heat discolouration
- ✓ Removing oxide layers
- ✓ Roughening
- ✓ Work on weld seams

Drive types

- ✓ Manual application
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13

51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com