

Extended Product Type: CAL16-11A

Product ID: SK829002-A

EAN: 7320500002964

Long Description:

2 pole screw type left side mounted auxilliary contact block, instantaneous N.O. and N.C. contacts, suitable for standard industrial environments

Technical Information: AUXILIARY CONTACT

Connecting terminals (delivered in open position):

M 3.5 (+,-) pozidriv 2 screw with cable clamp

Conventional Free-air Thermal Current (I_{th}):

acc. to IEC 60947-5-1, $\eta=40^{\circ}\text{C}$ 16 A

Customs Tariff Number: 85369001

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20

Minimum switching capacity [V/mA]: 0.25 VA/ 12 V / 5 mA

Package Level 1 Gross Weight: 0.064 kg

Power Loss: Per Pole 0.2 W

Product Net Weight: 0,05 kg

Rated Breaking Capacity acc. to IEC 60947-5-1: 10 x I_e AC-15

Rated Frequency (f_r):

Supply Circuit 50 Hz

Supply Circuit 60 Hz

Rated Insulation Voltage (U_i): acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V

Rated Making Capacity acc. to IEC 60947-5-1: 10 x I_e AC-15

Rated Operational Current AC-15 (I_e):

(220 / 240V) 6 A

(24 / 127V) 6 A

(380 / 440V) 4 A

(500V) 1 A

(690V) 1 A

Rated Operational Current DC-13 (I_e):

(125V) 1.8 A

(24V) 6 A

(250V) 0.6 A

(48V) 6 A

(72V) 4 A

Rated Short-time Withstand Current (I_{cw}):

for 0.1s 100 A

for 1.0s 50 A