

8001TZ
Pipe turnbuckle bodies, galvanized

CE

DIN 1478

TECHNICAL DATA

- safety factor: 4
- traceability code

LABORATORY TESTS

- chemical analysis
- tensile test

AVAILABLE CERTIFICATES

- Technical product specifications
- Test report UNI EN10204 type 2.2
- CE Declaration of Conformity



		art.	Ø mm	≈ "	WFL kg	L mm
	080010512	8001TZ M12	M12	1/2	690	125
	080010516	8001TZ M16	M16	5/8	1290	170
	080010520	8001TZ M20	M20	3/4	2130	200
	080010524	8001TZ M24	M24	1	3060	255
*	080010527	8001TZ M27	M27	1.1/8	4000	255
	080010530	8001TZ M30	M30	1.3/16	4860	255
	080010536	8001TZ M36	M36	1.3/8	6500	295
	080010542	8001TZ M42	M42	1.5/8	9700	330