

BIZ2 - Bizweld Work FR Jacket

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 22

Product information

The Bizweld FR Jacket provides the wearer with all day protection and comfort. Features include secure stud fasteners down the front and two chest pockets with flaps. This flame resistant jacket also includes a concealed mobile phone pocket.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Chest pockets with stud flap closure
- Stud adjustable cuffs for a secure fit
- Concealed stud front for easy access
- External standards label for quick identification of protection levels
- Available in sizes from XS to 5XL
- Radio loop for easy clipping of a radio
- Concealed phone pocket
- 3 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays

BIZ2 - Bizweld Work FR Jacket
Commodity Code: 6203321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/12872-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
BIZ2NARXS	Navy	43.0	28.0	46.0	0.6540	0.0554	5036108243617	25036108731859
BIZ2NARS	Navy	43.0	28.0	46.0	0.6960	0.0554	5036108046379	25036108607840
BIZ2NARM	Navy	43.0	28.0	46.0	0.7410	0.0554	5036108046386	25036108607833
BIZ2NARL	Navy	43.0	28.0	46.0	0.7730	0.0554	5036108046393	25036108607826
BIZ2NARXL	Navy	43.0	28.0	46.0	0.8230	0.0554	5036108046409	25036108607857
BIZ2NARXXL	Navy	43.0	28.0	50.0	0.8580	0.0602	5036108046416	25036108607864
BIZ2NARXXXL	Navy	43.0	28.0	50.0	0.9010	0.0602	5036108046423	25036108607871
BIZ2NAR4XL	Navy	43.0	28.0	50.0	0.8840	0.0602	5036108046430	25036108607819
BIZ2NAR5XL	Navy	43.0	28.0	50.0	0.9870	0.0602	5036108216475	25036108703672