



### Main

Range	Actassi
Product	Vertical ring
Product destination	Rack 800 mm wide
Additional features	Openable

### Complementary

Number of rack unit	1U
Maximum capacity	48
Material	Metal sheet: DC01 1.2 mm Plastic part: PA66 GF20 Plastic part: PC
Colour	Dark grey (RAL 7016) Light grey (RAL 7035)
Width	0.11 M 110 mm
Height	0.40 M 40 mm
Depth	100 Mm 0.100 m

### Environment

Temperature range	14...131 °F -10...55 °C
-------------------	----------------------------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations