



RSHEY25-TV-VA

Plummer block housing unit

Plummer block housing unit RSHEY..-TV-VA,
RIBB plastic

Technical information

Your current product variant

Special material	TV	Plastic housing
Corrosion resistant bearing	VA	Corrosion-resistant VA design
Material	TV	Plastic

Main Dimensions & Performance Data

d	25 mm	Bore diameter
L	76.2 mm	Length
H 2	73.5 mm	Height
≈m	0.344 kg	Weight

Mounting dimensions

J	50.8 mm	Distance fixing bore
K	M10	Thread fixing bore

Dimensions

H	36.5 mm	Distance shaft axis
A	39.5 mm	Width (base)
S	19.8 mm	Distance raceway
B	34.1 mm	Width
Q	1/4 - 28 UNF	Connection thread for lubrication



Additional information

GEH-SHE05-TV	Housing
GYE25-KRR-B-FA107-VA	Bearing designation
KASK05-S-G	End cap
KASK05-S-R-NBR	Open protecting cap

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	80 °C	Operating temperature max.