



R-085

Advanced impact and cut protection gloves, offering dexterous, comfortable hand protection



Impact

Abrasion Protection



Cold



Cut



Light Duty

Versatile impact and cut protection gloves, ensuring dexterous, comfortable hand safety

- **Specialized protection:** RINGERS® R085 work gloves' patented TPR (thermoplastic rubber) design, developed with F3 Technology™, ensures knuckles, thumb and full length of fingers impact protection
- **Advanced defenses:** A breathable knit shell ensures high-level cut resistance
- **Elevated comfort:** Their fleece-lined design keeps hands warm and comfortable in cold conditions, for versatile hand protection
- **Heightened grip:** These RINGERS® gloves' half-dipped nitrile palm coating, with a sandy finish, enhances wet and dry grip
- **Improved durability:** Their integrated TCR patch limits wear and tear
- **Enhanced features:** A high-visibility design improves hand safety, while touchscreen-compatible thumb tips, index and middle fingers enable safe technological interaction



Industries

- Automotive
- Mining
- Oil and gas
- Manufacturing
- Construction
- Automotive Aftermarket

Applications

- Makeup and breakout tools
- Running tools into the wellbore
- Handling explosives
- Assembly of parts
- Engagement and release of drill string slips
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- Set-up of pressure manifold and tubing injector head
- General pumping work
- Cold Storage
- Scaffolding
- Loading and hauling
- Assembling and mounting components



R-085

Advanced impact and cut protection gloves, offering dexterous, comfortable hand protection

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length impact protection
- **Breathable knit shell:** For impact gloves offering dexterous comfort
- **Fleece lining:** Sustained warmth and comfort in cold temperatures

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



EN388: 2016



4X44FP

Technologies



Touchscreen Compatible

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R085	Finishing: Dipped Coating Material: Nitrile Liner Material: HPPE Cuff Style: Knitwrist	13	7, 8, 9, 10, 11, 12, 13	Red	8 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

