

Rexel Meteor Half Strip 20 Sheet Metal stapler

Solidly constructed, compact metal stapler for stapling up to 20 sheets of paper. Ideal for every day use, it can be used for permanent stapling jobs or temporary pinning and tacking. With a 65mm throat depth, it staples up to 15 sheets using Rexel No. 56 (26/6) or up to 20 sheets with No. 16 (24/6) staples.



Colour	Number	EAN code
 black	2100019	5028252047722
 blue	2100020	5028252047739



Attributes

- Compact, metal stapler for stapling up to 20 sheets of paper (80 gsm)
- Ergonomic grip to ensure accurate and comfortable stapling
- Staples 15 sheets with No. 56 (26/6) staples and up to 20 sheets with No. 16 (24/6) staples
- Top loading refill mechanism making it quick and easy to refill staples
- Pinning and tacking function for display boards or temporary stapling
- Features a 65mm paper insertion depth for flexible stapling
- 5 year guarantee when using Rexel staples

Specifications

Number	2100019
Colour	black
Dimensions (W x H x D)	38 x 58 x 135 mm
Capacity of Stapling	20 sheet
Weight	150 g
Pallet quantity	1440
EAN code	5028252047722