



Product number 1154890010
EAN 4007123644292

DESCRIPTION

- Robust, break and impact resistant plastic casing.
- Suitable for robust wall mounting.
- With an ergonomic carrying handle for comfortable carrying.
- Pre-wired and ready for connection.
- Protective cover for fuses.
- With RCD circuit breaker 30 mA for extra safety.
- Earthed sockets 230 V with 3 phases.

TECHNICAL DATA

Max. current carrying capacity	16 A	Earthed socket outlets	4
Miniature circuit breaker	3	Plug system socket	Type F (Protective contact)
Residual current circuit breaker (RCCB)	FI with IFN 0.03 A (standard)	Supply/ connection option	Attachment plug
Rated current (FI)	30 mA	Plug system plug	CEE 16 A 3P+N+E (5p) 400 V
Number of poles (FI)	4	Degree of protection (IP)	IP44
CEE 400 V / 16 A / 3P+N+PE (5p) Steckdosen	2		

PACKAGING, DIMENSIONS AND WEIGHTS

Packaging	Coloured sales box	Dimension LxWxH (without packing)	28 cm x 34.9 cm x 12.2 cm
UP	1	Weight of product (including packaging)	3.22 kg
Weight of product (without packaging)	2.88 kg	Dimension LxWxH (incl. packing)	39 cm x 29 cm x 14 cm