



## RSL 0.5-PP10

Glass Tube Fuse, 500 mA, 5x20mm, Slow

### Product Properties:

Voltage type	AC/DC
Connection type	Base
Release characteristic	Time-lag (T)
Rated current	0.5 A
Rated voltage	250 V
Optical defect indication	No
Model	Glass fuse

### Dimensions:

MOQ	10 .
Unit	pck
Rated voltage	250 V
Dimensions	5x20 mm

### Approvals:

Voltage type	AC/DC
--------------	-------

### Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (247 Subs. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

### Other information:

---

<b>ETIM-Class</b>	EC002704 - Cylindrical fuse
<b>ETIM-Release</b>	9.0
<b>Trademark</b>	NECORE
<b>Product Group</b>	Glass tube fuses - Consumer pack
<b>Search Description</b>	GLASSÄKRING, 500 MA
<b>Alternative SKU</b>	RSL0.5-PP10

### **Logistic information:**

---

<b>Barcode</b>	733117638055
<b>Country of origin</b>	FR
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	10 .
<b>Stock code</b>	RSL 0.5-PP10
<b>Taric code</b>	85361010
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.