



Product data sheet

Power tools for trade & industry

Cordless Combi

GSB 18V-28 Professional



Durable all-rounder in a compact format

Part number: 0 601 9H4 001[> More product information](#)

Technical Data

webshop-pdp-section-technical-data-table-key-Technical data

Torque (soft/hard/max.)	28/63/- Nm
No-load speed (1st gear / 2nd gear)	0 – 500 / 0 – 1,900 rpm
Chuck capacity, min./max.	1.5 / 13 mm
Torque settings	20+1

webshop-pdp-section-technical-data-table-key-Battery and power

Battery voltage	18 V
-----------------	------

webshop-pdp-section-technical-data-table-key-Size and weight

Weight excl. battery	1.2 kg
----------------------	--------

Noise/vibration information

Drilling in metal

Vibration emission value ah	2,5 m/s ²
Uncertainty K	1,5 m/s ²

Impact drilling in masonry

Vibration emission value ah	13,5 m/s ²
Uncertainty K	1,5 m/s ²

Screwdriving

Vibration emission value ah	2,5 m/s ²
Uncertainty K	1,5 m/s ²

Noise

Sound pressure level	89 dB(A)
Sound power level	100 dB(A)
Uncertainty K	3 dB



Product data sheet

Power tools for trade & industry

Advantages

- Durable: Less wear thanks to 13 mm full metal chuck
- Long-lasting: Reduced risk of motor overload and long lifetime thanks to Electronic Motor Protection (EMP)
- Ergonomic: Comfortable handling due to the compact design

