

FEATURES

- Holding force of 500 N
- Provides a holding force when de-energised and release when pulsed
- Suitable for typical applications such as machine mechanisms, door/guard locking and remote hold/release requirements

RS PRO Access Control Door Magnet, 500N Holding Force 24V dc

RS Stock No.: 739-3223



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO electro-permanent magnets provide a holding force when de-energised and release when pulsed. These magnets are suitable for machine mechanisms, door/guard locking and remote hold / release requirements. Optimum performance when used with RS PRO armature plates (available separately): please see stock no [739-3211](#) etc. Energise to hold version available on example [739-3233](#).

This range of RS PRO magnets include the following types:

[739-3223](#) - 50mm Dia. 24V Electro Permanent Magnet

[739-3227](#) - 35mm Dia. 240V Electro Permanent Magnet

[739-3236](#) - 35mm Dia. 24V Electro Permanent Magnet

General Specifications

AC or DC Operation	DC
Failure Mode	No
Finish	Bright Nickel Plated with Machined Face
Application	Machine Mechanisms, Door/Guard Locking & Remote Hold/Release Requirements

Electrical Specifications

Supply Voltage	24Vdc
Power Consumption	8.5W

Mechanical Specifications

Holding Force	500N
Diameter	50mm
Length	94mm
Width	63mm

Protection Category

IP Rating

IP 54

Approvals

Compliance/Certifications

RoHS Certificate Of Compliance

