



182.72.104.66RPNAEinstell-Nadellager

Aligning needle roller bearings RPNA35/52-XL (Series RPNA) without inner ring

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	35 mm
D	52 mm
C	20 mm Tolerance: +/-0,5
D1	47,5 mm
rmin	0,8 mm
m	131 g Mass
Cr	27500 N Basic dynamic load rating, radial
C0r	41500 N Basic static load rating, radial
Cur	7300 N Fatigue limit load, radial
ng	12900 1/min Limiting speed

