

MLFB-Ordering data

6SE6400-2FL02-6BB0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

<b>Rated data</b>	<b>Connections</b>
-------------------	--------------------

<b>Input</b>	
Number of phases	1 AC
Line voltage	200 ... 240 V
<b>Output</b>	
Rated current	26.0 A

<b>Line side</b>	
Version	screw-type terminal
Conductor cross-section	1,5 ... 6,0 mm <sup>2</sup>
<b>Load side</b>	
Version	Pigtail
Cable length	0.43 m

<b>Mechanical data</b>
------------------------

<b>Dimensions</b>	
Width	149.0 mm
Height	213.0 mm
Depth	50.5 mm
Degree of protection	IP20 / UL open type
Net weight	1.0 kg

<b>PE connection</b>	
Version	M5 stud

<b>Standards</b>
------------------

Compliance with standards	CE / UL
---------------------------	---------