

Price* : 106.61 GBP



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Electronic hygrostat
Humidity setting range	20...80 %
Display type	OLED screen
Information displayed	Relative humidity

Complementary

Input voltage	200...240 V AC
Maximum switching capacity	4 A 230 V AC
Electrical connection	6 terminals 2.5 mm ²
Mounting mode	By screws Clipped
Height	External : 85 mm
Width	External : 56 mm
Depth	External : 44 mm
Mounting location	On mounting plate 35 mm DIN rail Spacial upright Cross rails
Ambient air temperature for operation	-40...80 °C
Hysteresis	3 %
Number of outputs	2 output(s) heating function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
