

A120 - Grip 13 PU Palm Glove

Collection: General Handling

Range: Hand Protection

Materials: Polyester, Elastic

Dipping:

Inner Pack: 12

Outer Carton: 288

Product information

Portwest's best selling glove is ideal for a wide range of different industries. Perfect for intricate tasks where dexterity and breathability are essential. Available in a wide range of colours with sizes ranging from 5/XXS - 12/3XL. Each pair is individually packed. These gloves are also available in different variants such as full carton of 288 pairs (AB129), vending ready packaging (VA120), touchscreen compatible (A195) and 2 latex elastic free versions (A123 and A128)..

General Handling

The general handling and grip glove category is one of the most popular collections within the Portwest hand protection range. A carefully selected range of coatings, including latex, nitrile, polyurethane and PVC, provides a broad range of styles suited to a diverse range of tasks.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (3131X)

ANSI/ISEA 105: 2016 CUT Level (A1)

ANSI/ISEA 105: 2016 ABRASION Level (3)

ANSI/ISEA 105: 2016 PUNCTURE Level (2)



Features

- Smooth PU coating for increased abrasion resistance
- Polyester is stronger than natural fibres and offers sufficient durability
- 13 gauge liner constructed for durability and precise fitting
- Silicone free - Ideal for manufacturing, paint applications, electronics and glass handling where silicone is problematic
- Perfect for intricate tasks
- Retail tag which aids presentation for retail sales
- Palm dipped to increase dexterity and ventilation
- CE certified
- CE foodsafe



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A120 - Grip 13 PU Palm Glove Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/15564-02/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A120O1RXS	Orange	65.0	45.0	45.0	0.0220	0.1316	5036108223992	15036108711540
A120O1RS	Orange	65.0	45.0	45.0	0.0220	0.1316	5036108223978	15036108711526
A120O1RM	Orange	65.0	45.0	45.0	0.0280	0.1316	5036108223961	15036108711519
A120O1RL	Orange	65.0	45.0	50.0	0.0260	0.1463	5036108223954	15036108711502
A120O1RXL	Orange	65.0	45.0	50.0	0.0260	0.1463	5036108223985	15036108711533
A120O1RXXL	Orange	65.0	45.0	50.0	0.0300	0.1463	5036108224005	15036108711557