

Pendant control

46-458.1818A

Distribution by
Rs-online



<https://rs-online.eao.com/component/46-458.18...>

Your product:



46-458.1818A Pendant control

FRONT

Colour: Grey

MOUNTING

Mounting cut-out: Ø 22 mm

Mounting type: Panel mounting

ELECTRICAL CHARACTERISTICS

Rated insulation voltage Ui: Ui 300V - Uimp 2.5KV (IEC-EN60947-1)

Pollution degree: 3

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Tightening torque: 0.8 ... 1.2 Nm (7.1÷10.6 Lb-in)

Weight: 0.4 kg

AMBIENT CONDITION

IP front protection: IP65, IP66

IK front protection: IK08

Operating temperature: – 35 °C ... + 80 °C

CERTIFICATE

Approbations: CSA, UL

Conformities:	CE
REACH:	REACH compliant
RoHS:	RoHS compliant
Standards:	CSA C22-2, IEC EN 60204-1, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Short Description:	Pendant control
Number of holes:	4 (3+1)
Dimension:	83 mm x 197 mm
Housing material:	Plastic
Product attributes:	Suitable for outdoor applications
Dimension drawings:	

