

Datasheet

6253-0039 Heavy Duty Footswitch 7719256

- Heavy duty die cast aluminium industrial footswitch
- Study durable industrial footswitch
- Stylish ergonomic design
- Yellow cover, black base
- M20 rear hole cable entry
- 10K potentiometer, DPCO, Snap action - at start of pedal depression
- Sealed to IP67
- Electrical Rating: 21A 250V AC, 1 HP 125V AC, 2HP 250V AC; Potentiometer: 0.5W 50V DC Max.
- Contact Gap: <3mm, suitable for mains
- Operating Temperature: -25°C to +60°C



Outline Dimensions

