

# A 50 -40 - Ferrule

3241240

<https://www.phoenixcontact.com/gb/products/3241240>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 40 mm, sleeve length: 40 mm, color: silver

## Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented

## Commercial data

Item number	3241240
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH3412
Product key	BH3412
Catalog page	Page 480 (C-3-2019)
GTIN	4046356908139
Weight per piece (including packing)	3.6 g
Weight per piece (excluding packing)	3.63 g
Customs tariff number	85369010
Country of origin	DE

# A 50 -40 - Ferrule

3241240

<https://www.phoenixcontact.com/gb/products/3241240>



## Technical data

### Notes

General	These ferrules are not included in DIN 46228-1: 1992-08
---------	---

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Long/short-term temperature: +105°C/+120°C

### Connection data

#### Conductor connection

Conductor cross section flexible max.	50 mm <sup>2</sup>
Conductor cross section AWG max.	1/0
Stripping length	40 mm

### Dimensions

Dimensional drawing	
Sleeve length	40 mm
Length contact range	40 mm
Maximum stripping length	40 mm
Ferrule diameter	10.3 mm
Sleeve wall thickness	0.3 mm
Inner dimensions of the insulating collar	13 mm

### Material specifications

Color	silver-colored
Material	CU-DHP
Coating	galvanically tin-plated
Surface characteristics	Tin-plated

### Mechanical properties

#### Technical data

Sleeve length	40 mm
---------------	-------

### Environmental and real-life conditions

# A 50 -40 - Ferrule

3241240

<https://www.phoenixcontact.com/gb/products/3241240>



## Ambient conditions

Permanent temperature	105 °C
Short-term temperature	120 °C

## Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

# A 50 -40 - Ferrule



3241240

<https://www.phoenixcontact.com/gb/products/3241240>

## Classifications

### ECLASS

ECLASS-13.0	27400201
-------------	----------

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# A 50 -40 - Ferrule

3241240

<https://www.phoenixcontact.com/gb/products/3241240>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)