

S-20 ; 0...600 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V

S-20 ; 0...600 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V

Item number: 14071275

Quantity: 1 pcs.

Order code: S-20-3-BG560-HD12K-A-AGGZZZ-ZWZ W1011S20Z-ZZZZA1Z3-
SS18LZ2APSZZE-ZZGDZZSAZZZS1

Overview: S-20 ; 0...600 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V
Pressure transmitter Model S-20
Non-linearity: 0.25% BFSL
Overpressure limit: see data sheet
Process connection: G 1/4 A DIN EN ISO 1179-2 ; Sealing: NBR
Pressure port: D 2.5 mm
Electrical connection: angular connector DIN 175301-803 A mating connector included
pin assignment el. connection: U+=1, U-=2
Permissible medium temperature: -20...+100°C
shock and vibration resistance: 100 g shock, 20 g vibration
Approvals: cULus
Test protocol: with test protocol

Details: S-20 ; 0...600 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V
Pressure transmitter Model S-20
Non-linearity: 0.25% BFSL
Overpressure limit: see data sheet
Process connection: G 1/4 A DIN EN ISO 1179-2 ; Sealing: NBR
Pressure port: D 2.5 mm
Electrical connection: angular connector DIN 175301-803 A mating connector included
pin assignment el. connection: U+=1, U-=2
Permissible medium temperature: -20...+100°C
shock and vibration resistance: 100 g shock, 20 g vibration
Approvals: cULus
Test protocol: with test protocol