

Fixing Clips

Stock item designed for body diameters of 24mm, 36mm, 45mm and 62mm. Allows fixing from either the top side of a ball deck or the underside where CL11 is not suitable. For deck thicknesses of up to 4mm.



General Specifications - CL14-15

| Dimension A - Max Diameter (mm) | 30.9 | | | | H |
|--|--------------|--------------|--------------|-------------|---------------|
| Dimension D - Body Diameter (mm) | 6 | | | | |
| Dimension E - Under Flange to Base (mm) | 0.3 | | | | |
| Flange Diameter A (mm) | 30.9 | | | | |
| Inside Diameter B (mm) | 24.7 | | | | |
| Clip Depth C (mm) | 6 | | | | |
| Material Thickness | 0.3 | | | | |
| Can be used with the following Ball Units: | <u>515-0</u> | <u>515-4</u> | <u>515-6</u> | <u>7104</u> | <u>810-15</u> |

CL14

