



Main

Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	PowerPact B Compact NSXm
Voltage release type	Undervoltage release
[Uc] control circuit voltage	277 V AC

Complementary

Threshold tripping voltage	0.35...0.7 x Un - during opening time 0.85 x Un - during closing time
Mounting mode	Clip-on
Response time	< 50 ms
Auxiliary connection terminal	Pre-wired 0...0.8 mm ² (AWG 18) stranded copper
Wire stripping length	8 mm
Cable length	1 m

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications