Sicad S.p.A.
Via Caduti della Liberazione, 57
21040 Uboldo (VA) – Italia
Tel: +39 02 964121 Fax: +39 02 96412294
Web: www.eurocel.it

# PRODUCT INFORMATION
# EUROCEL PP 500

## DESCRIPTION

Medium tensile palletizing single sided tape.

## PRODUCT DATA

| | |
|---|---|
| **Backing** | 0.050 mm MOPP film; orange, white, transparent |
| **Adhesive** | Synthetic rubber and resins |

| | Unit | Value | Method |
|---|---|---|---|
| **Total thickness** | mm | 0.072 | PSTC 133 |
| **Adhesion to steel** | N/25mm | 13 | PSTC 101 |
| **Tensile strength MD** | N/25mm | 415 | PSTC 131 |
| **Elongation at break** | % | 33 | PSTC 131 |
| **Temp. Resistance** | °C | 60°C | = |

## APPLICATION

Medium strength tensilized PP film suitable for standard palletizing.

| Features | Benefits | |
|---|---|---|
| Synthetic rubber and resins adhesive | ✓ High adhesion in most situations | ✓ Very sticky on several surfaces |
| MOPP backing | ✓ Good resistance at break<br>✓ Easy handling | ✓ High security in application |

## CONDITIONS OF USE AND CONFORMITY

Product shelf life and storage: 12 months; suggested storage temperature shall range from 15°C to 25°C with max. relative humidity of 65%. Material shall be stored away from heat sources and possibly kept in original package, avoiding light exposure as well. When temperature are lower than suggested, it is always required to recondition the tape at normal temperature before use. This information is given to the best of Sicad's knowledge. Values are typical and do not constitute a specification. Customers are required to do their own testing under their working condition for their intended application. Any liability arising in respect of our products will be limited to the value of those products charged to the customer excluding any consequential loss.



**Società Italiana Cellophane Adesivo**
P.I. e C.F. IT 00220060123
Iscrizione R.E.A. Varese n. 129175
Reg. Imprese Varese n. 00220060123
Capitale Sociale € 15.000.000 i.v.