



ENGLISH

Datasheet

25m Long Black Rubber Hose, Applications Air, Water, 16mm Inner Diam.

RS Stock number 486-485

Type : Air & Water Hose

Type No. : 2007

Application : Air / Water

S

Description :

Black compressed-air hose for pneumatic equipment, tools, compressors, etc. Also suitable for water. Fits standard claw couplings used in the building sector.

Working Temperature : -30°C to +80°C

Std. Branding : CODAN 2007 - AIR HOSE diM - 20 BAR WP - sn.

Reinforcement : Polyester

Inside : SBR

Colour : Black

Outside : SBR

Colour : Black

Standards : ISO 188/ISO 2398

Data

| Inside dia. mm | Outside dia. mm | Working Pressure BAR | Burst Pressure BAR | Bend Radius mm | Weight g/m | Product number |
|-------------------|--------------------|-------------------------|-----------------------|-------------------|---------------|-------------------|
| 10.0 | 18.0 | 20 | 60 | 70 | 300 | 2007010 |
| 13.0 | 23.0 | 20 | 60 | 91 | 450 | 2007013 |
| 16.0 | 26.0 | 20 | 60 | 112 | 550 | 2007016 |
| 19.0 | 30.0 | 20 | 60 | 133 | 650 | 2007019 |
| 25.0 | 36.0 | 20 | 60 | 175 | 900 | 2007025 |

Illustration

