



Data sheet

ENGLISH

PTO Control Valve, Push-Pull, 4/2, 6mm with remote reset

RS Stock No. : 784-0076



Specification

Manufacturers series	BHP
Mounting style	Panel/Body Mounted
Actuation type	Push-Pull Knob
Port connection	6mm
Function	4/2
Maximum Flow	300 l/min
Pressure range	0-16 bar
Minimum operating temperature	-10°C
Maximum operating temperature	+50°C