



Save as PDF



9420 LED Work Light



Now you can start your day before sunrise if you have the new portable Peli ProGear 9420 LED Work Light in your tool crib. Equipped with two LEDs (1000 lumens of light and 4 hours of burn time), plus a 1,5 m high mast deploys easily in seconds and illuminates your entire work area. With the 9420 you will get the job done without the hassle of power cords.

Accessing the basement or the attic is easy when you sling the lightweight and collapsible 9420 over your shoulder. The new Peli ProGear 9420 LED Work Light: Keeps you moving at the speed of light. • **Deploys to 1,5 m**

- **High/Low Water Resistant Switch**
- Battery and Charger included
- Click here for information on the [9420XL](#)

Light Source

LED Type	LED Life	Tested Lumen Value
Cree	50000	500 (Low) 1000 (High)
Lamp Heads	Number of LEDs	Beam Spread
1	2	58
Brightness Settings	IP Rating (Ingress Protection)	
2		

Power Source

Battery Type	Battery Burn Time	Battery Charging Time	Battery Life
Lithium ion	4 (Low) 2 (High)	2 hrs.	300
Low Battery Warning	12V Primary Sockets	12V Auxiliary Sockets	
Yes	1	0	
Watts		Voltage	
		0	

Dimensions & Weight

Head Length	Head Width	Head Depth
0cm.	0cm.	0cm.
Width Closed	Length Closed	Height Closed
0cm.	73.6cm.	0cm.
Mast Height Extended	Cord Length	Weight
157.4 cm.	0cm.	3.81kg.

Materials

Head	Body	Mast
Lens	Switch Type	
	Push Button Type	

Configuration

Cat. #	Description
9420	9420 LED Work Light

9420 LED Work Light Accessories

Cat. #	Description

Approvals

RoHS (Restriction of Hazardous Substances)
Compliant
