

## FEATURES

- **Sintered Bronze Material:** Offers high strength and excellent wear resistance, ensuring long-lasting performance.
- **0.88 in Inside and Outside Diameter:** Provides a compact solution suitable for a variety of applications.
- **0.12 in Thickness:** Ensures a slim profile for use in tight spaces.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Capable of handling significant dynamic loads, enhancing durability.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Supports high static loads, making it suitable for heavy-duty applications.
- **ISO 9001:2008 Certified:** Ensures quality and reliability, meeting international standards.

## RS PRO Sintered Bronze Thrust Washer, 0.88 in Diameter

RS Stock No: 528-887



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO sintered bronze thrust washer is designed to provide reliable support and reduce friction in axial load applications. Ideal for use in machinery and equipment where space is limited, it offers excellent performance under both dynamic and static loads.

## General Specifications

Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Thrust Washer
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Washer

## Mechanical Specifications

Inside Diameter	0.88 in
Material	Sintered Bronze
Outside Diameter	0.88 in
Thickness	0.12 in

## Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------