

## Features

- Corrosion-resistant screws
- Easy wiring installation
- Phenolic body
- Zinc-plated steel terminal screws

## RS PRO Term Strip Barrier 8Poles 15A 300V Phenolic

RS Stock No.: 458763



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

From RS PRO, this non-fused terminal block presents a reliable and cost-effective solution to wire to-wire connections. This lightweight and robust terminal block is designed for free hanging or panel mount applications.

## General Specifications

Fused	NO
Mounting Type	Free Hanging, Panel Mount
Contact Material	Brass
Termination Method	SCREW
Material	Phenolic
Number of Ways	8

## Mechanical Specifications

Optional cable size	22~14AWG
Suggested screw torque	9Ib.-in.
Operating Temperature	150°C maximum

## Electrical Specifications

Voltage Rating	300VAC RMS maximum
Current Rating	15A Amps maximum

## Approvals

Standards Met	UL Recognized
Declarations	CE/UKCA Declaration of Conformity

DIMENSION

