

FEATURES

- Ideal for general purpose use.
 Contacts are polarised to ensure correct connection
- Standard connector size
- Easy 'jab-in' connection for rapid termination, just push wire in and tighten screw
- IEC colour coded
- The International Electrotechnical Commission (IEC) is an international standards organisation that prepares and publishes international standards.

RS PRO Standard Quick Wire Thermocouple Connector Plug IS-E-MQ Type E IEC

RS Stock No.: 774-7276



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Easy 'jab-in' connection for rapid termination, just push wire in and tighten screw. Contacts are polarised to prevent incorrect connection.

General Specifications	
General Description	Contacts are polarised to prevent incorrect connection
Specifications	
Thermocouple Type	E IEC
Connector Type	Quick Wire Plug
Connector Size	Standard
Colour	Violet
Max. Temperature	220°C
Pins	Solid Round Pins
+Positive Contact	Nickel Chromium
-Negative Contact	Copper Nickel

Approvals

RoHS Compliant	Yes
Standards Met	BS EN 50212:1997. RoHS


Thermocouple Connectors Product Guide

A comprehensive family of miniature and standard Thermocouple Connectors, accessories, panels, terminal and barrier blocks. Available in IEC, ANSI & JIS colour specifications.

Click below to view:

RS Pro Thermocouple Connector Selection Guide





Standard in-line Plug - Quick Wire

(dimensions in mm)



RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:





RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:

