

Specifications for Bulk BMP71 Heatex Cable Markers

Article No.	622239
Brady Material No.	B-7643
Material Type	Thermoplastic Polyether Polyurethane
Colour	Yellow
Finish	Matt
Order Reference	BM71H-2-7643-YL
Printer Compatibility	BMP71
Size - Height (mm)	10.00
Size - Width (mm)	75.00
Thickness (mm)	0.45
Total Qty per Pack	250 Sleeve(s) / Box
Vertical Repeat (mm)	81.17
Approval/Compliance	Adherence: MIL-M-81531 AS (SAE-AS81531-1998) Point 3.4.2/4.6.2, Flame retardant, Halogen Free;Resistance to solvents: MIL-STD-202G test method 215(2002) (MIL81531/SAE-AS81531-1998 Clause 3.4.3.)
Ribbon Series	M71-R6000HF
Application	Voice & Data Communication; Wire & Cable Marking
Industry	Data & Telecommunications;Electrical
Description	These Heatex® markers contain no added halogens and offers excellent fire safety characteristics combined with minimal smoke emission.
Max. Characters per Line	51
Max. Lines of Text	4
Max. Service Temp. °C	90
Min. Service Temp. °C	-40
# of Holes	4
Shape	Rectangle