


FEATURES

- Flexible magnetic strip for use on ferromagnetic surfaces
- Fitted miniature flat pin plug
- JIS Type K thermocouple
- Japanese Industrial Standards (JIS) are the standards used for industrial activities in Japan

JIS MAGNETIC STRIP THERMOCOUPLE TYPE K PFA TWIN TWISTED WITH MINIATURE PLUG 1m

RS Stock No.: 2394668



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

A flexible magnetic strip thermocouple capable of being attached to most ferro-magnetic surfaces, the large area of the magnet ensures good adhesion allowing simplicity of installation. Useful in a wide range of temperature monitoring applications, particularly in test and development

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-50°C to +100°C
Construction	Magnetic strip 50 x 25 x 1mm
Measuring Junction	Positioned/seated in magnetic strip for surface measurement
Standards Met	JIS (Japanese Industrial Standards)
Application	Flexible magnetic strip for use on ferro-magnetic surfaces

Mechanical Specifications

Probe Diameter	Magnetic strip 50 x 25 x 1mm
Termination Type	Miniature Plug
Compensating Cable Length	1m
Cable Insulation	PFA 1/0.3mm

Approvals

Compliance/Certifications	RoHS Compliant
----------------------------------	----------------

Similar Products Range

	1m	2m
Cable Length	2394668	2394667

RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:

<p style="text-align: center;">rspro.com</p> <p style="text-align: center;">Temperature. It matters</p>	<div style="border: 1px solid red; padding: 5px; margin-bottom: 5px;"> <p style="text-align: right;">Best Sellers </p> </div> <p>Calibration</p> <p>Whether it's existing equipment or a new purchase, you need to have confidence in the accuracy of your measurements.</p> <p>That's where our calibration service can help.</p> <p>Purchase new products with confidence.</p> <p>A certificated calibrated sensor straight out of the box, ready to use.</p> <p style="text-align: center;">RTD Detectors</p> <p>Wire-wound type provides greater accuracy and stability but are vulnerable to shock.</p> <p>Flat film type are resistant to shock and have quicker thermal response times.</p> <p>Various lengths and diameters available, in class A, B and 1/10th Din.</p> <div style="border: 1px solid red; padding: 5px; margin-top: 10px;"> <p style="text-align: right;">Best Sellers </p> </div> <div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>ANSI SYSCAL Type K Mineral Insulated Thermocouple RS 181-7296</p> <p>IEC SYSCAL Type K Mineral Insulated Thermocouple RS 181-7288</p> <p>IEC SYSCAL Type J Mineral Insulated Thermocouple RS 181-7305</p> </div> <div style="width: 45%;"> <p>PT1000 Thin Film Detector RS 362-9907 Allied 70643582</p> <p>PT100 Wire Wound Detector RS 611-7839 Allied 70646151</p> <p>PT100 Wire Wound Detector RS 362-9799 Allied 70643577</p> </div> </div>
<p>Exposed Junction Thermocouples</p> <p>Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.</p> <p>1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.</p> <div style="border: 1px solid red; padding: 5px; margin-top: 10px;"> <p style="text-align: right;">Best Sellers </p> </div> <div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>ANSI Type K Exposed Junction RS 814-0134 Allied 70656459</p> <p>ANSI Type K High Temp Exposed Junction RS 131-4749 Allied 71080908</p> <p>IEC Type K Exposed Junction RS 363-0250 Allied 70643600</p> </div> <div style="width: 45%;"> </div> </div>	<p>Fabricated and Specialist Thermocouples</p> <p>Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.</p> <div style="border: 1px solid red; padding: 5px; margin-top: 10px;"> <p style="text-align: right;">Best Sellers </p> </div> <div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>Magnet Thermocouple RS 762-1115 Allied 70651739</p> <p>Heavy Duty Thermocouple RS 762-1128 Allied 70651743</p> <p>Rubber Patch Thermocouple RS 290-5036 Allied 70642886</p> </div> <div style="width: 45%;"> </div> </div>
<p>Thermocouple & PRT Cable</p> <p>Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC & Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.</p> <div style="border: 1px solid red; padding: 5px; margin-top: 10px;"> <p style="text-align: right;">Best Sellers </p> </div> <div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>IEC PVC Insulated Flat Pair RS 219-4573 Allied 70641630</p> <p>ANSI PFA Insulated Twin Twisted RS 814-0030 Allied 70656106</p> <p>IEC Glassfibre Insulated Flat Pair RS 236-3836 Allied 70641730</p> </div> <div style="width: 45%;"> </div> </div>	<p>Thermocouple Connectors</p> <p>Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.</p> <div style="border: 1px solid red; padding: 5px; margin-top: 10px;"> <p style="text-align: right;">Best Sellers </p> </div> <div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>IEC Thermocouple Plug RS 455-9764 Allied 70644391</p> <p>ANSI Thermocouple Socket RS 769-1127 Allied 70652125</p> <p>IEC Thermocouple PCB Socket RS 381-7570 Allied 70643749</p> </div> <div style="width: 45%;"> </div> </div>

RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:

 <p>Mineral Insulated Thermocouples</p> <p>Available in various calibration types with a variety of terminations. These include; Thermocouple plugs, Terminal heads and Thermocouple cable</p>	<p>Best Sellers </p> <p>IEC Thermocouple with PTFE Cable RS 397-1236 Allied 70643843</p> <p>IEC Thermocouple with Mini Plug RS 397-1488 Allied 70643863</p> <p>ANSI Thermocouple with PFA Cable RS 847-1019 Allied 70658112</p>	 <p>NEW PRODUCTS</p> <p>RS PRO, the own brand of RS Components, offers an unbeatable range of products across all industries with quality you can trust.</p> <p>New products are constantly added to improve the offering of our product range.</p>	<p>NEW PRODUCTS </p> <p>Brake Pad Temp Sensor RS 200-0601 Allied 72173869</p> <p>RTD Temp Sensor Hirschmann Style RS 200-0594 Allied 72173862</p> <p>Washer Thermocouple RS 200-0616 Allied 72173882</p>
 <p>Sensors with Industrial Terminal Heads</p> <p>Industrial sensors housed in a stainless steel sheath and terminal head protection to IP67. Available as a thermocouple or Pt100.</p>	<p>Best Sellers </p> <p>Type K 300mm Long RS 787-7829 Allied 70653306</p> <p>Type K 200mm Long RS 787-7816 Allied 70653303</p> <p>Type K 100mm Long RS 787-7804 Allied 70653235</p>	<p>www.rspro.com</p>  <p>www.alliedelec.com</p>	
 <p>L60 Fine Wire Thermocouple Welder</p> <p>The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.</p>	<p>Best Sellers </p> <p>L60 Fine Wire Thermocouple Welder RS 363-0351 Allied 70825788</p> 		